

Product information

13MM PERCUSSION DRILL



Satisfying the professional's needs

HP1631K

Max. in steel	13 mm
Max. in masonry	16 mm
Max. in wood	30 mm
No Load Speed	0 - 3200 rpm
Blows per minute	0-480000 bpm
Input wattage	710 w
Vibration: Drilling	2.5 m/sec ²
Vibration K factor	1.5 m/sec ²
Net weight	1.9 kg



- Forward/reverse rotation
- Variable speed
- Double Insulation
- Plastic carrying case.

Details correct as of: 12-10-2015

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com