TECHNICAL DATASHEET
SPORTS SAFETY TRAINER

HECKEL
PERFORMANCE WITH STYLE

SNEAK-R BLACK LOW

PRODUCT CODE	SIZES	WIDTH	WEIGHT*
78053	35 > 52	11	590 g

i-PUREnrj planet clima zone ESD 100% metal free

Made in Italy

EN 20345:2022 + A1:2024

S3S FO SR

AREAS OF APPLICATION







Active Stability



COMPOSITION

OUTSOLE	PU i-PUREnrj planet
UPPER	water-repellent full-grain leather rear Active Stability TPU reinforcement
CLOSING SYSTEM	laces with eyelets
LINING	distance-mesh
TONGUE	breathable textile and mesh with gussets
TOE CAP	non-metallic composite
PERFORATION-RESISTANT MIDSOLE	non-metallic textile
INSOLE	top in non-woven textile bottom in porous PU memory foam forefoot and heel shock absorbers

OPTIONS

MULTIPLE FIT SYSTEM	available in widths 10 and 12 by replacing the insole

KEY FEATURES

- HIGH-PERFORMANCE CUSHIONING AND ENERGY RETURN WITH I-PURENRJ PLANET
- ACTIVE STABILITY SUPPORT STRUCTURE FOR ENHANCED STABILITY
- WATER-REPELLENT UPPER DELIVERS ENHANCED PROTECTION AGAINST MOISTURE
- PROTECTION AGAINST FINE PERFORATION RISKS UP TO 3.0 MM (PS)
- WIDE RANGE OF SIZES, WIDTHS AND WOMEN'S LAST 35 > 40

*per foot in size 42

UVEX HECKEL s.a.s. • 44 Rue d'Engwiller - La Walck, 67350 Val-De-Moder (France) • **Tel.** +33 (0)3 88 07 61 08
France email contact.france@uvex-heckel.fr • **Export email** contact.export@uvex-heckel.fr • **www.heckel.fr**

TECHNICAL DATASHEET
SPORTS SAFETY TRAINER

HECKEL
PERFORMANCE **WITH STYLE**

PACKAGING

SALES UNIT	1 pair
QUANTITY PER CARTON	10 pairs

ACCESSORIES

INSOLE WIDTH 10	67962
INSOLE WIDTH 11	67963
INSOLE WIDTH 12	67964

ADDITIONAL REQUIREMENTS

Oil-resistant outsole **FO**

Slip resistance (ceramic tile floor + glycerine) **SR**

SUSTAINABILITY

PRODUCT

FREE FROM HARMFUL SUBSTANCES PER **UVEX LIST, EXCEEDING REACH REQUIREMENTS**

7% RECYCLED MATERIALS
ACCORDING WITH ISO 14021

COMPOSITION

OUTSOLE	15% recycled PU granules from production waste
PERFORATION-RESISTANT MIDSOLE	21% recycled polyester

PACKAGING

SHOE BOX MADE FROM
90% RECYCLED MATERIALS

INSTRUCTIONS FOR USE MADE FROM
100% RECYCLED MATERIALS

CARBON FOOTPRINT

10.6 KG CO_2E CRADLE-TO-CUSTOMER
12.15 KG CO_2E CRADLE-TO-GRAVE
CALCULATION DATE: 07/2026*

PRODUCTION

ISO 14001-CERTIFIED
PRODUCTION SITE IN CEVA (ITALY)

*__Calculation method:__ IPCC 2021 GWP100a, in accordance with ISO 14067 • **Database/Software**: Company-specific calculation based on SimaPro and ecoinvent • **Functional unit**: single product, or a pair where products are used in pairs • **Scope**: Cradle-to-Grave • Unit: kg CO2e • The CO2e values stated apply to the defined calculation period and are subject to change at any time..

CE certified PPE • **Update**: 09/2026 • UVEX HECKEL s.a.s. reserved the right to change product features without notice • photos and documents are non-contractual

UVEX HECKEL s.a.s. • 44 Rue d'Engwiller - La Walck, 67350 Val-De-Moder (France) • **Tel.** +33 (0)3 88 07 61 08
France email contact.france@uvex-heckel.fr • **Export email** contact.export@uvex-heckel.fr • **www.heckel.fr**