



P.C. LAYOUT



SWITCHING DIAGRAM



non-shorting

Specifications:

- Contact rating: 0.3A, 125V AC
- Contact resistance: 20mOhm max.
- Insulation resistance: 100MOhm min. at 500V DC
- Dielectric strength: 500V AC
- Mechanical life: 10 000 cycles
- Operating force: 150 +/-100gf
- Material: Frame: POM
Slider: PPE+PS
Base: PBT
Terminal: brass, silver plated
Contact: phosphor bronze, silver plated



Tolerances: ±0.2mm	Date	Name
	12/13	dr

MFP 261 N

knitter-switch

30 29 82

Page
1/1

Modifications	Date	Name
---------------	------	------