



Main

Range of product	Mureva Styl
Product or component type	Cable entry
Range compatibility	Mureva Styl
Quantity per set	Set of 10

Complementary

Number of cables	1
Thread type	M20
Cable entry	Easy valve access
Condition of use	Indoor/outdoor
Material	PP (polypropylene) SEBS
Colour tint	Grey
Length	49 mm
Height	13 mm
Width	42 mm
Chemical and detergent products resistance	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Quality labels	NF AENOR
IP degree of protection	IP55
IK degree of protection	IK08

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes

RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations