



Linetrimmer LXT®

DUR190L

18V • 3 500 – 6 000 min⁻¹ • 230 /
255 / 300 mm

**Model DUR190L is a brushless line trimmer powered by
18V Li-Ion battery**

Powerful line trimmer with a loop handle for trimming gardens and other outdoor areas. Equipped with automatic torque drive technology (ADT). Low vibration and noise levels and good ergonomics ensure a good user experience.

LXT BL ADT AFT
MOTOR

Technical specifications

Nominal Battery Voltage	18 V
No load speed	3500 / 5100 / 6000 min ⁻¹
Cutting width	230 / 255 / 300 mm
Tool weight with battery	2,7 - 3,0 kg
Nylon line- Diameter	2,0 mm
Sound Power Level (L _{WA})	85,9 - 91,6 dB(A)
Sound Pressure Level (L _{pA})	74,0 - 77,0 dB(A)
Product Dimensions (L x W x H):	1836 x 348 x 236 mm
Brushless Motor	✓
Voltage LXT	✓
Spindle Thread	M10 x 1,25 LH
Handle Type	L
Vibration Level, Metal 4-Blade	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Metal 4-Blade	1,5 m/s ²

User benefits

- Low power consumption thanks to brushless motor
- ADT (Automatic torque Drive Technology) adjusts speed and torque during operation for optimum performance
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- A protective hood for metal sheet, plastic knife and line head
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

■ Optional AC

198893-8

Trimmer Head 2,0 mm, M10 x 1.25



831304-7

Accessory Bag



■ Other

User manual

Parts drawing