



PRODUCT DATASHEET

Datasheet creation date: 2025/07/09 7:44 (UTC)



6302

Single-Row Deep Groove Ball Bearings



Boundary Dimensions

d	15	mm	Bore diameter
D	42	mm	Outside diameter
B	13	mm	Width
r (min.)	1	mm	Chamfer dimension

Basic Load Ratings

Cr	12600	N	Basic dynamic load rating
C0r	5450	N	Basic static load rating

Speeds

Grease	19000	min-1	Grease lubrication
Oil (Oil-bath)	24000	min-1	Oil-bath lubrication

Abutment and Fillet Dimensions

da (min.)	20	mm	Diameter of shaft abutment
da (max.)	22.5	mm	Diameter of shaft abutment
Da (max.)	37	mm	Diameter of housing abutment
ra (max.)	1	mm	Radius of shaft or housing fillet

Calculation factors

fo	12.3		Factor
----	------	--	--------

Additional information

z	7		Number of Balls
Dw	7.938	mm	Ball Diameter

Mass

Mass approx.	0.083	kg	Mass approx.
--------------	-------	----	--------------

