

FEATURES

- **Sintered Bronze Material:** Provides durability and resistance to wear, ensuring long service life.
- **Flanged Design:** Facilitates easy installation and alignment, enhancing operational efficiency.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with moderate dynamic loads, ensuring reliable performance.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads, offering versatility in use.
- **Outside Diameter of 20.05 mm:** Compatible with a wide range of housings, providing flexibility in application.
- **Bore Size of 14.02 mm:** Ensures a precise fit for shafts, reducing vibration and noise.

RS PRO 14.02 mm Flanged Plain Bearing

RS Stock No: 529-026



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable and efficient rotational movement. Made from sintered bronze, it offers excellent performance in reducing friction between moving parts, making it ideal for various industrial applications.

General Specifications

Bore Size	14.02 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	20.05 mm
Width	20 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------