

AI-GB 1-10 RD-20000 - Ferrule



2100097

<https://www.phoenixcontact.com/gb/products/2100097>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ferrule, Length contact range: 10 mm, sleeve length: 16 mm, color: red

Your advantages

- Due to the increased diameter of the insulating collar, this type of ferrule is specifically used with AWG cables
- These ferrules enable practical crimping of conductors with increased insulation

Commercial data

Item number	2100097
Packing unit	20,000 pc
Minimum order quantity	50,000 pc
Sales key	BH341S
Product key	BH341S
GTIN	4067923214347
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85369010
Country of origin	DE

AI-GB 1-10 RD-20000 - Ferrule



2100097

<https://www.phoenixcontact.com/gb/products/2100097>

Technical data

Product properties


Product type	Cable end sleeve
Conductor category	stranded conductors, class 2, 5, 6 / B, C, K, M
Product property	Suitable for AWG/multi-standard cables due to the increased diameter of the insulating collar
	UL certified
	Made from soft tin-plated electrolytic copper
	Correspond to the requirements of UL 486F
	Plastic collar made of polypropylene
	Halogen-free
	Long/short-term temperature: +105°C/+120°C

Connection data

Conductor connection

Conductor cross section flexible max.	1 mm²
Conductor cross section AWG max.	18
Stripping length	13 mm

Dimensions

Dimensional drawing	
Sleeve length	16 mm
Length contact range	10 mm
Maximum stripping length	13 mm
Ferrule diameter	1.5 mm
Sleeve wall thickness	0.15 mm
Insulating collar thickness	0.3 mm
Inner dimensions of the insulating collar	3.4 mm

Material specifications

Color	red (RAL 3001)
Flammability rating according to UL 94	HB
Coating	galvanically tin-plated
Surface characteristics	Tin-plated
Components	free from silicone and halogen

Mechanical properties

Technical data

AI-GB 1-10 RD-20000 - Ferrule



2100097

<https://www.phoenixcontact.com/gb/products/2100097>


Sleeve length	16 mm
---------------	-------

Standards and regulations

Design according to standard	Color code in accordance with DIN 46228-4, UL 486F-E
------------------------------	--

Drawings

Dimensional drawing



Sleeve length (b), length contact range (h), insulating collar inner dimension (d), sleeve diameter (k), insulating collar thickness (i), sleeve wall thickness (j)

AI-GB 1-10 RD-20000 - Ferrule



2100097

<https://www.phoenixcontact.com/gb/products/2100097>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2100097>



cULus Listed

Approval ID: E488001

AI-GB 1-10 RD-20000 - Ferrule



2100097

<https://www.phoenixcontact.com/gb/products/2100097>

Classifications

ECLASS

ECLASS-13.0	27400201
-------------	----------

ETIM

ETIM 9.0	EC000005
----------	----------

AI-GB 1-10 RD-20000 - Ferrule

2100097

<https://www.phoenixcontact.com/gb/products/2100097>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk