

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Cordless Hedgecutter

PRO GHE 18V-50



Ergonomic design with outstanding cutting performance and easy handling

The most important data

Battery voltage	18.0 V
Blade length	50 cm
Tooth opening	23 mm

Part Number 0 600 8C9 500

Technical data

Technical data

Battery voltage	18.0 V
Blade length	50 cm
Tooth opening	23 mm
Battery recommendation	$\geq 4.0\text{Ah}$
Cutting speed	1,500 rpm
Stroke rate at no load nominal	3,000 spm
Weight excl. battery	2.9 kg
Packaging dimensions (width x length x height)	245 x 1075 x 220 mm

Noise/vibration information

Total vibration values

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Powerful brushless motor for high performance and long service life
- Its 50 cm blade cuts thicker branches without jamming thanks to the patented Bosch Anti-Blocking System
- Easy handling due to the low weight, ergonomic design, and optimal balance – ideal for longer work



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

