



## Product Datasheet

ENGLISH

# G 1/8 ATEX Solenoid-Spring Valve, 5/2



*RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.*

### Technical data

<b>Manufacturers Series</b>	MD
<b>Mounting Style</b>	Free-standing
<b>Function</b>	5/2
<b>Port Connection</b>	G 1/8"
<b>Actuation</b>	Single Solenoid / Spring Return
<b>Maximum Flow</b>	450 l/min
<b>Solenoid Voltage</b>	24Vdc
<b>Solenoid Power Consumption</b>	1W
<b>Minimum Operating Tempertaure</b>	-10 °C
<b>Maximum Operating Temperature</b>	+50 °C