



CYLINDRICAL CHIPPING HAMMER 10MM RC1205

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:11:53





DESCRIPTION

CYLINDRICAL CHIPPING HAMMER 10MM

MULTIPURPOSE Its 2,100 hits/min strike rate means it can be used for multiple tasks: cutting sheet metal or rivets, chiselling, stamping, cleaning concrete mixers... And folding the edges of bodywork panels. Comfortable chisel hammer ideal for continuous use. Sheathed handle insulated against the cold. Silent exhaust. Uses accessories with a 10 mm cylindrical shank. Damped impact...

STANDARDS / DIRECTIVES

2006/42/CE

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:11:53



SPECIFIC DATA

Designation	AIR CHISEL ANTI-VIBRATION 10.2MM
Sales reference	RC1205
L (mm)	280
Weight (g)	2900
l (mm)	60
h (mm)	90
Piston stroke mm	88.9
Vibration (m/s ²)	7,5
Noise level (dBa)	95
C mm	6
C min mm	1/4
C mm	2 100
C mm	10.2
Aluminium rivet maximum diameter mm	
Guarantee	M2 SAM Equipment and Machine Guarantee

Guarantee applied

M2 | SAM Equipment and Machine Guarantee

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

[>> Find out more](#)

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

