

RS Pro 20 Way Unscreened Flat Ribbon Cable, 12.7 mm Width, 30m

RS Stock No. 424-2006

Brand RS Pro



Product Details

High Density 0.635mm Pitch Ribbon Cable

High density centre-to-centre pitch allows increased miniaturisation

Precise spacing for controlled electrical characteristics

Easy, fast mass-termination

The first conductor easily identified via continuous black edge trace

Double contour allows termination from either side of the cable

Solid 30awg conductors on 0.635mm (0.025in) spacing

UL style 2678

Note

Speedbloc® is a trade name of RS Components Ltd.

High Density

Ribbon cables provide a simple, quick and cost-effective solution to mass termination. They also have space and weight saving advantages over other wiring methods. They are therefore ideal for use on computers, peripherals, and interface units, audio and digital equipment.



Warning

These cables are not to be regarded as power cables or cables for the direct connection of equipment to mains power supplies.

Specifications

Not what you're looking for? Select the attributes you require, then click the button below

<input type="checkbox"/>	Number of Ways	20
<input type="checkbox"/>	Pitch	0.64mm
<input type="checkbox"/>	American Wire Gauge	30
<input type="checkbox"/>	Reel Length	30m
<input type="checkbox"/>	Width	12.7 mm
<input type="checkbox"/>	Cable Shape	Ribbon
<input type="checkbox"/>	Sheath Colour	Grey
<input type="checkbox"/>	Voltage Rating	150 V
<input type="checkbox"/>	Screened/Unscreened	Unscreened
<input type="checkbox"/>	Conductor Strand Type	Solid
<input type="checkbox"/>	Number of Strands	1
<input type="checkbox"/>	Minimum Operating Temperature	-20°C
<input type="checkbox"/>	Maximum Operating Temperature	+105°C
<input type="checkbox"/>	Capacitance	62.32 pF/m
<input type="checkbox"/>	Characteristic Impedance	80 Ω
<input type="checkbox"/>	High Density	Yes
<input type="checkbox"/>	Size of Strands	30 AWG
<input type="checkbox"/>	Core Strands	1/30