

# Drawn cup needle roller bearings with open ends HK2524-2RS (Series HK..-2RS)

lip seals on both sides, to DIN 618

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system ([https://www.schaeffler.de/content.schaeffler.de/en/news\\_media/index.jsp](https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp)) or by telephone on +49 (91 32) 82 - 28 97.

Fw	25 mm	
D	32 mm	
C1	24 mm	Tolerance: 0/-0,3
rmin	0,8 mm	
m	40 g	Mass
Cr	19900 N	Basic dynamic load rating, radial
C0r	33000 N	Basic static load rating, radial
Cur	4300 N	Fatigue limit load, radial
nG Fett	6100 1/min	Limiting speed for grease lubrication

