



Hand protection

VENICUTD08

LONG-LASTING CUT WORK

Level D cut-resistant glove, ideal in dry conditions



Specific benefits



Performance

· The anti-slip properties of the polyurethane coating provides good grip.



Cost-effective

· User-friendly worksite package, including three pairs for weekly use

Applications

- Public works
- Building
- Finishing works / Craftsmanship
- Maintenance
- Automotive
- Mining

Certifications and norms



EN 388
4 X 4 2 D

ANSI ISEA 105

A4

Protects against risks



Cutting



Wearing



Hand protection

VENICUTD08

LONG-LASTING CUT WORK

Level D cut-resistant glove, ideal in dry conditions

Standards - Details



EN388:2016+A1:2018

4 [0-4] ABRASION RESISTANCE
X [0-5] CUT RESISTANCE
4 [0-4] TEAR RESISTANCE
2 [0-4] PIERCE RESISTANCE
D [A-F] CUT RESISTANCE ISO 13997

Technical details

Glove kind	Mechanical glove
Glove family	Knitted coated glove
Mechanical glove kind	Knitted
Coating material and finition	PU
Coating level	Palm coated
Number of layer	Single layer
Gauge	13
Benefits element	Reach, Vendor pack
Color	Grey
Size	7, 8, 9, 10, 11
Type of packaging	Pack of 3



Safety gloves

VENICUTD08

LONG-LASTING CUT WORK

Level D cut-resistant glove, ideal in dry conditions

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
VECUTD08GRG307	Grey	07	VENICUTD08	3295249192037	13295249192034	40	4	10.08 kg	31.0 cm	62.0 cm	34.0 cm
VECUTD08GRG308	Grey	08	VENICUTD08	3295249192044	13295249192041	40	4	11.03 kg	31.0 cm	62.0 cm	34.0 cm
VECUTD08GRG309	Grey	09	VENICUTD08	3295249192051	13295249192058	40	4	11.85 kg	31.0 cm	65.0 cm	35.0 cm
VECUTD08GRG310	Grey	10	VENICUTD08	3295249192068	13295249192065	40	4	12.72 kg	31.0 cm	62.0 cm	36.0 cm
VECUTD08GRG311	Grey	11	VENICUTD08	3295249192075	13295249192072	40	4	11.6 kg	32.0 cm	58.4 cm	39.0 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height