

Main

Product or component type	Mechanical lug
Accessory / separate part type	Connection kit
Poles description	4P

Complementary

Quantity per set	Set of 1
Location of connection	Downstream Upstream
[In] rated current	15...125 A for copper 15...100 A for aluminium
Conductor material	Steel
Connections - terminals	Screw terminal - 1 cable(s) 2.5...95 mm ² (AWG 14...AWG 3/0) - solid Screw terminal 2.5...95 mm ² (AWG 14...AWG 3/0) - stranded Screw terminal 2.5...70 mm ² (AWG 6...AWG 2/0) - fine stranded
Control wire terminal	10 A for 0.5...6 mm ² (AWG 20...AWG 10), stranded or fine stranded 10 A for 1.5...6 mm ² (AWG 20...AWG 10), rigid

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
PVC free	Yes
Halogen content performance	Halogen free product