

FEATURES

- Ideal for cleaning and repairing damaged or corroded threads
- Hss construction of the pieces in the set allows for easy and clean cutting into metals
- Durable and longer tool life
- Offers all the tools needed for intermediate tapping
- Taps can be used with a tap wrench or power tool

RS PRO HSS M12 Spiral Flute Tap Tap Set

RS Stock No.: 340-6568



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Threading Taps



Product Description

Introducing the RS PRO left-handed thread hand tap set. This high-quality set features all the essential pieces of equipment and accessories needed to successfully clean or cut new threads on fasteners, holes and much more. The HSS (High-Speed Steel) material makes it easier to cut harder materials with precision and efficiency, so this set is ideal for the professional craftsman or general engineering and automotive applications.

General Specifications

Thread Size	M12
Туре	Spiral Flute Tap
Thread Standard	Metric
Contents	M3; M4; M5; M6; M8; M10; M12
Number of Pieces	7
Standard	ISO
Applications	Automotive applications and repair, General maintenance workshops, DIY, Machinery repair

Mechanical Specifications

Material	HSS
Maximum Tap Size	M12
Minimum Tap Size	M3





