



Part Number : [1200910023](#)
Product Description : Nano-Change (M8) Field Attachable Connector, 3 Poles, Straight, Male, Unshielded, Screw Termination, Cable Diameter 3.50-5.00mm
Series Number : 120091
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : N03MA03134



Documents & Resources

Drawings
[1200910023_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; Imidazolidine-2-thione per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	120091
Description	Nano-Change (M8) Field Attachable Connector, 3 Poles, Straight, Male, Unshielded, Screw Termination, Cable Diameter 3.50-5.00mm
Approvals	cCSAus certified
IP Rating	IP67
Product Name	Nano-Change (M8)
Type	Field Attachable Connector
UPC	889056411936

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V

Physical

Cable Diameter	3.50-5.00mm (.138-.197")
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	None
Material - Connector Body	PA
Material - Contact	Brass
Material - Coupling Nut	Zinc Die-Cast, Nickel-Plated
Material - Plating Mating	Gold
Net Weight	8.500/g

Orientation	Straight
Poles	3
Temperature Range - Operating	-40°C to +85°C
Wire Size (AWG)	20-26

Mates With / Use With

Mates with Part(s)

Description	Part Number
Nano-Change (M8) Field Attachable Connector, 3 Poles, Straight, Female, Unshielded, Screw Termination, Cable Diameter 3.50-5.00mm	<u>1200910024</u>