


## FEATURES

- **DALI2, Push Dimming, PWM compatibility:** Offers versatile dimming options for enhanced lighting control.
- **1.25 A driver current:** Ensures consistent power supply to connected LEDs.
- **100-277 V AC input voltage:** Supports a wide range of input voltages for global compatibility.
- **IP20 rating:** Suitable for indoor use, providing basic protection against dust.
- **Constant Voltage operation:** Delivers stable voltage output for reliable LED performance.
- **Screw terminal type:** Facilitates easy and secure connections.

## RS PRO 30W LED Driver, 24V Constant Voltage

RS Stock No: 642-773



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

The RS PRO 30W LED Driver is designed for efficient power management in LED lighting systems. It provides a constant voltage output of 24V, making it ideal for applications requiring stable and reliable power delivery. With a maximum output power of 30W, this driver is suitable for a variety of LED configurations, ensuring optimal performance and longevity.

### General Specifications

Dimming Operation	DALI2, Push Dimming, PWM
Number of Outputs	1
Operating Modes	Constant Voltage
Primary Type	AC
Product Type	LED Driver
Sub Type	Constant Voltage LED Driver
Terminal Type	Screw

### Electrical Specifications

Driver Current	1.25 A
Input Voltage	100-277 V ac
Input Voltage Type	AC
Maximum Output Power	30 W
Output Voltage	24 V

### Protection Category

IP Rating	IP20
-----------	------

### Approvals

Standards/Approvals	CE, EN55015, EN61000-3-2, EN61000-3-3, EN61000-4-2,3,4,5,6,11, EN61347-1, EN61347-2-13, EN61547, EN62493, UL8750
---------------------	--