

Product data sheet

Specifications

Limit switch lever, 9007, arm t+ft +options



9007B1

Main

Range of product	9007
Series name	Severe duty
Product or component type	Limit switch lever
Device short name	9007T/FT
Associated head	9007BS9 9007CS9 9007T5S9 9007T10S9 9007NS9 9007AS9
Associated complete product	9007FT 9007T 9007C..S9
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever length: 38.10 mm - offset: - convertible roller
Type of roller	1 steel outside roller (convertible) diameter: 19.05 mm - width: 6.35 mm
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By 30° cam
Net weight	0.05 kg

Environment

Ambient air temperature for operation	-23...85 °C
Ambient air temperature for storage	-23...85 °C
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	45.359 g

Package 1 Height	2.032 cm
Package 1 width	2.54 cm
Package 1 Length	5.842 cm
Unit Type of Package 2	PAL
Number of Units in Package 2	4000
Package 2 Weight	310.711 kg
Package 2 Height	101.6 cm
Package 2 width	101.6 cm
Package 2 Length	121.92 cm
Unit Type of Package 3	S01
Number of Units in Package 3	50
Package 3 Weight	3.97 kg
Package 3 Height	15.0 cm
Package 3 width	15.0 cm
Package 3 Length	40.0 cm

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	18 months
----------	-----------