

BM ID-MAG20 - Magazine



1044356
<https://www.phoenixcontact.com/gb/products/1044356>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Infeed magazine for accommodating a max. of 20 UniCard sheets

Commercial data

Item number	1044356
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG121Z
Product key	BG121Z
Catalog page	Page 33 (C-3-2019)
GTIN	4055626620770
Weight per piece (including packing)	698 g
Weight per piece (excluding packing)	698 g
Customs tariff number	84439990
Country of origin	DE

Technical data

Product properties

Product type	Magazine
--------------	----------

Material specifications

RoHS compliant	yes
----------------	-----

Environmental and real-life conditions

Ambient conditions	
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

1044356

<https://www.phoenixcontact.com/gb/products/1044356>

Classifications

ECLASS

ECLASS-13.0	19140192
-------------	----------

ETIM

ETIM 9.0	EC001675
----------	----------

UNSPSC

UNSPSC 21.0	43211600
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------