



See online
technical sheet

/ MS41 13

1000V Insulated ratchet ring spanner 6-sided

/ Standards

- Standards : NF EN 60900, IEC 60900



/ Use

The tool enables high-torque tightening to be carried out very quickly in hard-to-reach areas.

/ Advantages

- The thickness of the insulation on the working head has been reduced to ensure excellent accessibility
- Easy to use; can be reversed by turning the tool over

/ Technical specifications

- Clamping key kind : isolate
- Length (mm) : 160
- clamping-key-opening-size : 13
- Sides number : 6 sides
- General acceptance (mm) : 15
- Recovery angle : 5°