

Datasheet

RS Pro Distribution Block

RS Stock No: **868-0736**



Product Details

RS Pro 2-way earth block in green/yellow colour, has a nylon housing construction for longer life. This earth block has high current fingerproof screwdown terminals for easy termination. The earth block supports 4 to 14 AWG cables of 6 to 35 mm² CSA. It is current rated for 76 A and voltage rated for 800 V. It measures 57.5 x 12 x 65 mm.

Features and Benefits

- Fingerproof terminals (to VBG4 requirements)
- Flammability rating UL94V-0
- Cable sizes from 6 - 35 mm²
- Mounting method DIN rail (top hat rail)/G-rail



ENGLISH

Specifications:

Colour	Blue
Height	43 mm
Housing Material	PC
Length	99 mm
Maximum Operating Temperature	+85°C
Number of Ways	26
Termination Method	Screw
Width	40 mm
Wire Size	35 mm ²
Standards Met	IEC 695-2-1; IEC 695-2-2; UL 94V-0; CE Certified