



MiniMark + MarkWare (Continental Europe)



The Brady MiniMark™ Industrial Label Printer offers an affordable sign and label making system that is compact, fast, and incredibly versatile. -Small / Compact: Mini conveys the compact nature of the machine. Easy to attach to a PC. - Fast: Print speed is faster than any other models in the range. (up to 4" per second). - Versatile: It can print on both Die-cut and continuous labels, increasing the range of applications.

Specifications

Article Number: 710141

Order Reference: MiniMark + MarkWare (Continental Europe)

Max. Labels per Day: 750

Max. Label Width (mm): 100

Max. Print Width (mm): 94

Max. Print Height (mm): 95

Max. Print Length (mm): 1,000

Print Resolution (dpi): 203

Power Supply: 230V (110V)

Keyboard: No

PC Connectivity: Yes

Peripheral Printing: Yes

Portability: No

Stand Alone Printing: No

Connectivity Options: LPT, USB

Memory: No

Built-in Fonts: None. Uses all available fonts on PC

Built-in Symbols: 0

Tape Widths: 29, 57, 100 and die cut labels

Input: PC

Continuous vs Die Cut Labels: Continuous & Die Cut Labels

Colour Capability: Single Colour

Bar Code Capability: Yes

Bar Code Type: 1D (Linear)

Dimensions - Width (mm): 203

Dimensions - Height (mm): 178

Dimensions - Depth (mm): 267

Weight (kg): 2.2