

## 894 75

### Single open ended spanner

metric

Code	ETIM
6577780	EC002130
EAN	UNSPSC
4010886657775	27-11-17-06
Country of origin	eCl@ss
Germany	21-04-01-01
Customs tariff number	
82041100	



### Article description

- Acc. to DIN 894, ISO 3318
- Manganese phosphate finish up to 38 mm, steel-grey up from 41 mm
- Size 10 - 135 mm with angling hole
- Carefully forged and professionally machined:
- Jaw: ground precisely to exact nominal size for optimum contact areas
- Jaw set at 15°
- Secure grip thanks to profile shaft - very ergonomic and handy
- Overloading indicated by deformation
- \* not standardised

### Article information

Contents (Qty of pieces)	1	Standard	DIN 894 ISO 3318
Net weight [kg]	2,782 kg	Width across flats 1 [mm]	75
Total length [mm]	600 mm	Head height 1 [mm]	20,7 mm
Total width [mm]	150 mm	Width of head 1 [mm]	152,0 mm
Total height [mm]	22 mm	Jaw set	15 °
Surface	steel-grey	Ratchet function	no
Material	Vanadium steel 31CrV3		