

UIC 558 13PIN PLUG KIT-MC-AG-CGM



Image is for illustration purposes only. Please refer to product description.

Part number	09 58 013 1021
Specification	UIC 558 13PIN PLUG KIT-MC-AG-CGM
HARTING eCatalogue	https://harting.com/09580131021

Identification

Category	Connector sets
Series	HARTING UIC
Identification	UIC 558
Element	Connector sets
Specification	With cable gland

Version

Termination method	Crimp termination
Gender	Male
Number of contacts	13
Number of cable entries	1
Cable entry	1x Integrated
Details	Crimp contacts enclosed separately

Technical characteristics

Conductor cross-section	0.75 ... 1 mm ²
Conductor cross-section [AWG]	AWG 18 ... AWG 17
Rated current	10 A
Rated voltage	60 V
Insulation resistance	>10 ⁷ Ω
Contact resistance	≤4 mΩ
Stripping length	5 mm
Limiting temperature	-50 ... +125 °C



Pushing Performance
Since 1945

Technical characteristics

Mating cycles	≥10,000
Degree of protection acc. to IEC 60529	IP69 / IPX9K acc. to ISO 20653 mated condition
Clamping range	12.9 ... 13.6 mm

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	Black
Material (seal)	Silicone
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	UIC 50558
	IRS 50558
	IEC 61373 Category 2
	IEC 60529

Commercial data

Packaging size	1
Net weight	7 g
Country of origin	India
European customs tariff number	85366990
GTIN	5713140190146
ETIM	EC002635
eCl@ss	27440115 Circular connector (set)