



Main

Range of product	Thorsman
Product name	Goliath 100
Product or component type	Work lamp
Light source	Compact fluorescent tube 21 W

Complementary

Type of installation	Outdoor Indoor
[Ue] rated operational voltage	230...240 V
Plug pole configuration	2P
Plug standard	European
Light source type	Glare-proof Flicker-proof
Luminous flux	1300 lm
Bulb lifespan	8000 h
Colour rendering index	R _a =82
Colour temperature	3500 K
Illuminance	3 m : 50 lux 1 m : 480 lux
Cable insulation material	Neoprene
Housing material	PC + rubber
Electrical connection	2.5 m H05RN-F2x1.0 feed power cord
Electrical insulation class	Class II
Marking	F ENEC 14
Height	205 mm
Width	209 mm
Depth	70 mm
Product weight	1 kg

Environment

IP degree of protection	IP54
Quality labels	CE ENEC
Ambient air temperature for operation	-15...50 °C