

## FEATURES

- Ensures high protection against dust and ingress
- Optional cage guard for three-point mounting version
- Surge protection for safety against peak voltage
- Versatile for application to any vehicle

## RS PRO Incandescent Beacon, 12 V dc, 24 V dc, Rotating, Surface Mount

RS Stock No.: 236-284



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

This Rotating Filament Beacon from our own RS PRO brand offer high quality solutions for industrial environments and process applications. It uses a mirror style reflector which spins around a permanently lit bulb, creating a powerful beam of light.

### General Specifications

<b>Bulb Type</b>	Incandescent
<b>Light Effect</b>	Rotating
<b>Lens Colour</b>	Lens not included
<b>Magnetic type</b>	Yes
<b>Housing Colour</b>	Black
<b>Lamp Include</b>	Yes
<b>Multifunction</b>	No
<b>Number of LED</b>	1
<b>Special Features</b>	Robust Three Point Fixing

### Electrical Specifications

<b>Supply Voltage</b>	12VDC,24VDC
<b>Current Type</b>	DC

### Mechanical Specifications

<b>Dimensions</b>	207mm (h)
<b>Base Diameter</b>	166mm
<b>Mounting Style</b>	Surface Mount

## Operation Environment Specifications

Maximum Temperature	-30°C
Minimum Temperature	+50°C

## Protection Category

IP Rating	IP 56
-----------	-------

## Approvals

Standards Met	RoHS Compliant
---------------	----------------

