



ENGLISH

RS Pro Datasheet

Flexible, smooth, orange hose for liquefied petroleum gas (LPG), propane/butane, to EN 16436-1 Class 2. The hose is primarily for use in assemblies of LPG applications.

For use with barbecues, patio heaters, caravan installations and weed burners.

The hose is DG-approved for sizes 6.3 - 10.0

Please contact Codan for further information.

Application: LPG / Propane / Butane

Standard Length: 25 metres

Working Temperature: -30°C to 80°C

Inside: NBR

Colour: Black

Reinforcement: Ester

Outside: EPDM

Colour: Orange

Standards: EN 16436-1 Class 2 / EN 16436-1:2014

Inside dia. (mm)	Outside dia. (mm)	Working Pressure BAR	Burst Pressure BAR	Bend Radius (mm)	Weight (g/m)
4,0	11,0	10	30	35	110
6,3	13,3	10	30	40	141
8,0	15,0	10	30	-	173
9,0	16,0	10	30	45	195
10,0	20,0	10	30	47	216