



heat exchanger, air-to-air, specific thermal output 36 W/K, 230 V AC RAL 7035, 316x 771x 103 mm (WxHxD), degree of protection IP54

Model		
product brand name	SIVACON	
product designation	air-air heat exchanger	
design of the temperature control	without thermostat	
design of the control cabinet cooler	Air/air	
type of voltage of the operating voltage	AC	
operating voltage		
• at AC at 50 Hz rated value maximum	230 V	
• at AC at 60 Hz rated value maximum	230 V	
Product details		
product component		
• heating	No	
• thermostat	No	
Mechanical Design		
height	771 mm	
width	316 mm	
depth	103 mm	
installation location	Control cabinet...panels, door	
Approvals Certificates		
General Product Approval	other	Environment



[Confirmation](#)

[Environmental Con-  
firmations](#)

### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR6423-5ML36>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR6423-5ML36>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8MR6423-5ML36](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR6423-5ML36)

CAx-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

---

last modified:

4/15/2025 

