



6313DDU

Single-Row Deep Groove Ball Bearings

Boundary Dimensions

d	65	mm	Bore diameter
D	140	mm	Outside diameter
B	33	mm	Width
r (min.)	2.1	mm	Chamfer dimension

Basic Load Ratings

Cr	102000	N	Basic dynamic load rating
C0r	60000	N	Basic static load rating

Speeds

Grease	3400	min-1	Grease lubrication
--------	------	-------	--------------------

Abutment and Fillet Dimensions

da (min.)	76	mm	Diameter of shaft abutment
da (max.)	85.5	mm	Diameter of shaft abutment
Da (max.)	129	mm	Diameter of housing abutment
ra (max.)	2	mm	Radius of shaft or housing fillet

Calculation factors

fo	13.2		Factor
----	------	--	--------

Additional information

z	8		Number of Balls
Dw	23.812	mm	Ball Diameter

Mass

Mass approx.	2.11	kg	Mass approx.
--------------	------	----	--------------

