



Main

Range	Thorsman
Product or component type	Cable reel
Device application	Power supply
[Ue] rated operational voltage	240 V
[In] rated current	13 A
Number of power socket outlets	4

Complementary

Cable length	30 m
Cable stiffness	Flexible
Quantity per set	Set of 1

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications