

Synchronous time switch Day 1 change-over contact 230V/50Hz
Surface-mounting



Model	
Product brand name	SENTRON
Product designation	Timers
Design of the product	Day
Design of the switching function	CO contact
General technical data	
Manner of function	<ul style="list-style-type: none"> • line-synchronous Yes • quartz-controlled No
Shortest switching time interval / of channel 1	30 min
Supply voltage	
Supply voltage / initial value	230 V
Supply voltage / Full-scale value	230 V
Supply voltage frequency	<ul style="list-style-type: none"> • minimum 50 Hz • maximum 50 Hz
Type of voltage / of the supply voltage	AC
Protection class	

Protection class IP	IP20
---------------------	------

Switching capacity

Switching capacity current / at AC / at 250 V / Rated value	16 A
---	------

Product details

Product feature / floating switching contact	Yes
--	-----

Product function

Product function	
• 60 min time program	No
• Automatic daylight-saving adjustment	No
• direct operation	Yes
• annual time program	No
• Switching preselection	Yes
• 24-hour time program	Yes
• Weekly time program	No

Number

Number of channels	1
--------------------	---

Mechanical Design

Height	110 mm
Width	69 mm
Depth	34 mm
Mounting type	others
Net weight	196 g

General Product Approval	Declaration of Conformity	other
---------------------------------	----------------------------------	--------------



[Environmental Confirmations](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=7LF5301-0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/7LF5301-0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=7LF5301-0

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

