

Adapter

AD-G1/4-1/4NPT-I

Part number: 9396

FESTO



 General operating condition

Data sheet

Feature	Value
Nominal size	7.95 mm
Operating pressure complete temperature range	-0.95 bar ... 10 bar
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque pneumatic connection 1	11 Nm
Max. tightening torque pneumatic connection 2	12 Nm
Nominal torque	9.05 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	24.22 g
Pneumatic connection, port 1	Male thread G1/4
Pneumatic connection, port 2	Female thread 1/4 NPT
Note on materials	RoHS-compliant
Material seals	PVC
Material housing	Galvanised steel