



Main

Range	Odace
Product or component type	Cable outlet
Device presentation	Cover plate with fixing frame
Product specific application	Exit wire for electrical heating
Type of packing	Paint cover

Complementary

Device mounting	Flush
Rated current	16 A
Fixing mode	By screws
Colour tint	Cobalt blue
Surface finish	Glossy
Connections - terminals	Screw terminals
Number of loop terminals	2
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1 x 1.5...1 x 2.5 mm ² for rigid cable(s) 1 x 1.5...1 x 2.5 mm ² for flexible cable(s) 1 x 1.5...1 x 2.5 mm ² for stranded cable(s)
Cable outer diameter	6...12 mm
Wire stripping length	12 mm
Material	Thermoplastic ABS-UV stabilised: centre plate PBT (polybutylene terephthalate) GF30: support frame
Height	71 mm
Width	71 mm
Depth	39 mm
Embedding depth	11.7 mm
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...35 °C
Standards	UTE C 61-392 EN 60669-1
Product certifications	LCIE: NF 603415A NF
IK degree of protection	IK04
IP degree of protection	IP2XC

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Minimum percentage of recycled plastic content	14