



Current
transformers
DM3TA2000
Split-core

Product designation

Product type designation

Type of CT

Current inputs

Primary current I_{pn} (/5)	A	2000
Operational frequency	min max	Hz Hz 50 60
Secondary output current	A	5
Overload withstand I_{pn}	%	120
Burden	cl. 1 VA	17

Insulations

Rated insulation voltage U_i IEC/EN	V	720
IEC rated short-time thermal current I_{th}	I_{th} for s	40...60
IEC rated dynamic current I_{dyn}	I_{th} for s	2.5
Insulation dry type		Class E


Mechanical features

Terminals type		Screw
Fixing		Screw fixing
Weight	g	1250

Ambient conditions

Temperature	Operating temperature	min max	°C °C	-25 +50
	Storage temperature	min max	°C °C	-40 +80
Relative humidity			%	90
Protection degree				IP30

Dimensions



Certifications and compliance

Certifications

IEC/EN 60044-1

Compliance

EAC

ETIM classification

EC000066 - Power contactor, AC switching