

# CYLOX™ One with inside key length 1: (30-40 / 30-40)

Seite 1 von 2



## YOUR DOOR, YOUR RULES

Manage access to your home, rental properties or interior spaces such as offices with the CYLOX One in an uncomplicated, secure and flexible way via app. Activate the smart cylinder with a touch, turn the knob and you're in.

Do you want to grant controlled access to your home or certain rooms to changing people, such as care services, tradespeople or cleaning staff? Do you want your family to have keyless access to your home? Or do you manage holiday accommodation and want to easily organise access for changing guests? Manage individual access authorisations for your door with the ABUS One app instead of the key and equip it with a security upgrade: the smart electronic cylinder CYLOX One offers SKG\*\*\*-tested drill protection and increased resistance to tampering. It is also suitable for tenants, as cylinder replacement does not usually require the landlord's permission. Recommended for doors with glass insert: Lock your door from the inside and remove the key. Even if a burglar breaks the glass, they cannot simply open the door.

Control your CYLOX One remotely with the BRIDGE One and integrate it into your smart home. In addition to the app, you can integrate separately available accessories and use a remote control or a finger scanner, for example. Enjoy keyless convenience combined with reliable ABUS security with the smart cylinder.

## Technologies

- High security thanks to ABUS SmartX™ technology, AES 128-bit encryption and ABUS Keycard for admin authentication
- Maximum flexibility thanks to the modular cylinder construction
- Powered by replaceable battery (1 x CR2 battery included)
- SKG\*\*\*-tested drill protection with hardened pins
- Special pins provide increased resistance to tampering
- Dustproof and waterproof according to IP67 certification
- Three coded keys included
- Compatible with: Bluetooth® remote control (CFF3100), Bluetooth® keyboard (CFT3100) and Bluetooth® finger

# CYLOX™ One with inside key length 1: (30-40 / 30-40)

Seite 2 von 2

scanner (CFS3100)

## Operation and use

- Recommended for doors with glass insert: Removed key prevents manual opening from the inside in the event of an attempted break-in through a smashed window – for doors with Euro profile cylinder
- Cylinder length can be customised to the door thickness thanks to the modular construction
- Can be combined keyed alike with other ABUS cylinders
- Easy operation with the ABUS One app on a smartphone or smartwatch, by code input, finger scan or keystroke
- Send access authorisations and limit them in time or share permanent access
- Remote access possible with the optionally available BRIDGE One

## Variants

- Finish: NM = Nickel Matt - high-quality, matt nickel-plated surface
- With inside key or inside knob

## Technical data - CYLOX™ One with inside key length 1: (30-40 / 30-40)

|                       |                     |
|-----------------------|---------------------|
| ABUS One App          | Yes                 |
| Bluetooth             | Yes                 |
| Bluetooth standard    | 5.1                 |
| Drill protection      | Yes                 |
| Security card         | Yes                 |
| Weight                | 284 g               |
| Wi-Fi                 | No                  |
| access control        | Yes                 |
| colour                | nickel matt         |
| emergency feature     | Yes                 |
| fire resistance doors | No                  |
| reversible key        | Yes                 |
| type of cylinder      | Electronic cylinder |
| EAN                   | 4003318409240       |