



Fuse-link, medium voltage, 31.5 A, AC 24 kV, 2", 51 x 442 mm, back-up, DIN, with striker

EL Number
(Norway)

24TDMEJ31.5
2809021

General specifications		
Product name		Eaton Bussmann series medium voltage DIN fuse
Part no.		24TDMEJ31.5
EAN		5027590245852
Product Length/Depth		442 millimetre
Product height		51 millimetre
Product width		51 millimetre
Product weight		2274 gram
Compliances		VDE 0670-4 DIN 43625 IEC 60282-1
Certifications		IEC Rated
Product Tradename		None
Product Type		Medium voltage DIN fuse
Product Sub Type		None
Electrical data		
Amperage Rating		31.5 A
Voltage rating		24 kV
Breaking capacity		50 kA
Performance Cat According To IEC 60282-1		Back-up
Rated frequency - min		50 Hz
Class		Class back-up
Resistance		46.8 Ohms
Product specifications		
Application		indoor or outdoor use transformer protection
Fuse indicator		With Striker
Fuse size		51 x 442 mm
Standard		DIN
Mounting method		Clip-in
Compatible fuse clip		
Used with		A3354710 Fuse clip 270303 Fuse clip

Technical data ETIM 9.0

Circuit breakers and fuses (EG000020) / Medium/high voltage fuse (EC003507)		
Electric engineering, automation, process control engineering / Electrical installation, device / Miniature circuit breaker system (MCB) / Medium-/high voltage fuse (ecl@ss13-27-14-19-11 [AGA534005])		
Rated current	A	31.5
Rated voltage	kV	24
Voltage type		AC
Rated frequency	Hz	50 - 50
Breaking capacity	kA	50
Utilization category		Other
Application		Primary side transformer protection
Length	mm	442
Diameter	mm	51
Performance category according to IEC 60282-1		Back-up
With striker		Yes

Standard			DIN
Release characteristic			Other
Installation technique			Air