

Item number: 64403

**Hand Brush S /
Nailbrush, 130 mm,
Hard, Blue**



The large dimensions of this nailbrush facilitates quick effective nail cleaning. The bristles are stiff enough to be effective but fine enough to reach under the nail area without causing damage to the skin. The hole in the base allows you to link a stainless steel cable to the wall or sink.

Technical data

Gtin-13 Number	5705020644030
GTIN-14 Number	15705020644037
Commodity Code	96039099
Suitable for Food Contact (EU 1935/2004), DoC	Yes
FDA compliant raw material (CFR 21)	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
Use of Phthalates (e.g. Bisphenol A)	No
Is Halal compliant	Yes
Bristle Description	Hard
Visible bristle length	17 mm
Material	Polypropylene, Polyester, Stainless Steel
Colour	Blue
Box Quantity	25 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	4000 Pcs
Box Length	285 mm
Box Width	195 mm
Box Height	180 mm
Length	130 mm
Width	50 mm
Height	40 mm
Gross Weight	0.106 kg
Net Weight	0.1 kg
Cubik metre	0.00026 M
Country of origin	Denmark
Max cleaning temperature (Autoclave)	121 °Celsius
Max. cleaning temperature (Dishwasher)	93 °Celsius
Max. usage temperature (for food contact)	40 °Celsius
Max usage temperature (non food contact)	80 °Celsius
Min. usage temperature	-20 °Celsius
Min. pH-value in usage concentration	2
Max. pH-value in Usage Concentration	10.5

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended

use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.