
Features

- Lockout solution for safe pipeline maintenance and repair.
- Fully conceals flange bolts, preventing unauthorised access or removal of the blind.
- Prevents blind removal until the safety padlock is removed, enhancing worker safety.
- Heavy-duty aluminium and hardened steel construction for superior durability indoors and outdoors.
- Compatible with standard lockout padlocks, supporting safe and compliant lockout/tagout procedures.

RS PRO Metallic Blind Flange Lockout - Large

RS Stock No.: 0750835



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- *A robust Blind Flange Lockout designed to physically secure pipeline blinds during maintenance or repair operations.*
- *The device completely covers and conceals flange bolts, ensuring they cannot be accessed or tampered with until the job is complete.*
- *Features an adjustable cup mechanism that locks out access to the nuts holding the blind in place.*
- *Provides workers with confidence that the pipeline blind will remain secured until the lockout padlock (sold separately) is safely removed.*
- *Built with durable aluminium and hardened steel, the device is engineered to withstand harsh indoor and outdoor environments.*

General Specifications

Type	Blind Flange Lockout
Material	Powder Coated Aluminium Die-Casted and Hardened Steel Rod
Colour	Red
Padlock holes	36
Package	BOPP

Mechanical Specifications

Nut Diameter	52.3 – 69.9mm
Pipe Diameter Range	335.6 – 609.6mm
Pipe Flange Width Range	197 – 448mm
Weight	1900 Grams

Operation Environment Specifications

Withstand temperature	-40°C – 93.3°C