



verso mobile storage bench with 3 drawer cabinet / 3 drawer cabinet.  
Featuring a robust, steel channel framework with integrated storage units  
125mm diameter castors and a 30mm multiplex wood worktop. Delivered  
assembled. Equivalent cabinet - WxDxH:525/800x550x600mm. Drawer  
configuration: 2x 125mm, 4x 175mm with 100% extension slides (75kg U.D.L.).  
Finished in durable powder coat paint in RAL 7035 light grey / RAL 7035 light  
grey. WxDxH: 1500x600x830mm.

Breite [mm]: 1500  
Tiefe [mm]: 600  
Höhe [mm]: 830  
Bruttogewicht [kg]: 130.53  
EAN-Code: 5039350103005  
Zolltarifnummer UK: 94032080  
Ursprungsland: GB

## Produkteigenschaften

|                      |               |
|----------------------|---------------|
| Product surface      | Powder coated |
| Product material     | Sheet steel   |
| Main colour          | Light grey    |
| Main RAL colour      | RAL 7035      |
| Secondary colour     | Light grey    |
| Secondary RAL colour | RAL 7035      |

## Artikelbeschreibungen

|               |       |
|---------------|-------|
| Product brand | verso |
|---------------|-------|

## Schubladen

|                           |     |
|---------------------------|-----|
| Number of drawers         | 6   |
| Drawer load capacity [kg] | 75  |
| Drawer height 1 [mm]      | 125 |
| Drawer height 2 [mm]      | 175 |
| Drawer height 3 [mm]      | 175 |

|                      |     |
|----------------------|-----|
| Drawer height 4 [mm] | 125 |
| Drawer height 5 [mm] | 175 |
| Drawer height 6 [mm] | 175 |

## Schrank, Gehäuse, Werkbank und EAP

|                          |                 |
|--------------------------|-----------------|
| Worktop/housing top type | Beech Multiplex |
|--------------------------|-----------------|