Narrow crown stapler LXT®,

DST630

18V, 9.5 - 38mm

Model DST630 is a 38mm narrow crown stapler compatible with 18Ga narrow crown staples, powered by an 18V LXT Li-Ion battery.

Featuring a pneumatic spring mechanism, it is reliably able to drive 18Ga narrow crown staples up to 38mm in length into hard materials such as LVL, similar feel to a pneumatic stapler. Slim nose for easy aiming. Tool-less nail jam clearing. Anti-dry fire mechanism



Technical specifications

Voltage LXT	✓
Staple Crown Width	5,7 - 6,35 mm
Staple range	9,5 - 38 mm
Fastener Magazine Capacity	110
Nominal Battery Voltage	18 V
Sound Pressure Level (L_{pA})	79 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s²
Vibration Uncertainty (K Factor)	1,5 m/s²
Tool weight with battery	2,8 - 3,1 kg
Product Dimensions (L x W x H):	246 x 96 x 282 mm
Staple measures	5,7 - 6,35 x 9,5 - 38 mm
Fastener Gauge	18 Ga
Product net weight	2,5 kg
Depth Adjustment	✓

User benefits

- Ergonomic soft grip handle provides increased comfort
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions

Link to product - www.makitauk.com

Related products

Other

User manual

Parts drawing