

PRODUCT-DETAILS

TY46MT

CABLE TIE 50LB 7IN NAT NYLON ID TPL



General Information

Extended Product Type	TY46MT
Product ID	7TAG009510R0033
EAN	5414363065005
Catalog Description	CABLE TIE 50LB 7IN NAT NYLON ID TPL
Long Description	Identification Cable Tie - Triple Strap Configuration, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/215 Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 185mm (7.3 Inches), Width of 4.8mm (0.19 Inches), Thickness of 1.3mm (0.05 Inches), Tensile Strength Rating of 220 Newtons (49 Pounds), Marking Pad Size of 46.mm (1.8Inches) x 28mm (1.1 Inches), Military Specified (MIL-SPEC MS3368-4-9)

Ordering

EAN	5414363065005
UPC	786210825229

Dimensions

Product Net Width	0.19 in 4.81 mm
Product Net Depth / Length	7.25 in 184.15 mm

Container Information

Package Level 1 Units	500 piece
Package Level 2 Units	1000 piece
Package Level 2 Width	9.1 in 231 mm
Package Level 2 Height	11 in 279 mm
Package Level 2 Depth / Length	13.3 in 338 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19680418
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	NYLON CABLE TIES AND ACCESSORIES

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000576
Instructions and Manuals	TY46MT

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5040 >> I.D. Ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

