

SENTRON, cylindrical fuse link, 10 x 38 mm, 2 A, gPV, Un DC: 1000 V



Figure similar

Model		
product brand name	SENTRON	
product designation	Cylindrical fuse link	
General technical data		
operating class of the fuse link	gPV	
type of voltage of the operating voltage	DC	
supply voltage at DC	1 000 V	
Main circuit		
operational current rated value	2 A	
Product details		
product component striker	No	
Mechanical Design		
mounting position	Any, preferably vertical	
net weight	8 g	
Approvals Certificates		
General Product Approval	other	Environment



[Confirmation](#)

[Environmental Confirmations](#)

Further information
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875
Information- and Downloadcenter (Catalogs, Brochures,...) http://www.siemens.com/lowvoltage/catalogs
Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW6002-4
Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3NW6002-4
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW6002-4
CAX-Online-Generator http://www.siemens.com/cax
Tender specifications http://www.siemens.com/specifications

