



9415Z0

9410L + SAFETY = 9415Z0

Everything that's great about the 9410L LED Lantern, plus safety certificates

At just 1.4kg (3 pounds) and 530 lumens, the 9415Z0 LED Lantern packs the power without the weight. Four LEDs, powered by the latest generation Ni-MH batteries illuminate a distance of 272 meters. And it's loaded with innovative technology and features you have come to expect from Peli.

Safety certified for the most volatile work areas, the 9415Z0 LED Lantern is safe and one of the most compact, high output lanterns on the market. Certified to ATEX Zone 0 (Category 1)



DIMENSIONS

Length 8.75" (22.2 cm)

MATERIALS

Body Anti-static Impact Modified PC/PBT
O-Ring EPDM
Lens Anti-static coated Polycarbonate (PC)
Shroud Anti-static Impact Modified PC/PBT

COLOURS

High Visibility Yellow

LIGHT SPECS

Lamp Type LED

POWER

Battery Size C
Battery Type NiMH
Battery Quantity 4
Batteries Included yes
Rechargeable yes
Charge Time 5 hrs 30 mins
Battery Level Indicator RGB LED
Volts 4.8v

WEIGHT

Weight With Batteries 58.2 oz (1650 gr)

SWITCH

Switch Type Push Button
Light Modes High / Low / Flashing

CERTIFICATIONS

ATEX Zone 0
IECEx ia






OTHER

Minimum Pack 1
Package Code B

Peli

c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999

info@peli.com www.peli.com

FL1 STANDARD	HIGH	LOW
	530 LUMENS	202 LUMENS
	4h 30mins	11h 30mins
	272m	166m
	18480cd	6914cd
	IPX4	

ACCESSORIES