

## FEATURES

- Ceramic cartridge
- T Speed rated
- 5mm x 20mm cartridge size

## RS PRO, 10A Ceramic Cartridge Fuse, 5 x 20mm, Speed T

RS Stock No.: 563-592



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

RS PRO anti-surge ceramic cartridge fuses which are designed to prevent damage to electrical equipment. These fuses allow an electric current to flow through until the current goes over the fuses rating then it will blow and stop the flow of electricity. This range of ceramic cartridge fuses are 5 x 20mm with a T speed rating.

## General Specifications

<b>Fuse Speed</b>	T
<b>Body Material</b>	Ceramic
<b>Application Category</b>	GRL
<b>Includes Indicator</b>	No
<b>Size Designation</b>	Miniature
<b>Applications</b>	

## Electrical Specifications

<b>Current Rating</b>	10A
<b>Voltage Rating</b>	250V ac
<b>High Rupture Capacity</b>	Yes
<b>Breaking Capacity (at Maximum Voltage Rating)</b>	1500A
<b>Resistance</b>	0.0050 $\Omega$

## Mechanical Specifications

<b>Fuse Size</b>	5mm x 20mm
<b>Overall Length</b>	20mm
<b>Diameter</b>	5.2mm
<b>Overall Dimensions</b>	5.2mm x 20 mm

## Operation Environment Specifications

<b>Maximum Operating Temperature</b>	125°C
<b>Minimum Operating Temperature</b>	-55°C

## Approvals

<b>Compliance/Certifications</b>	CSA Acceptance, UL Recognised, RoHS Compliant, BSI, PSE, KTL, CQC, VDE, SEMKO Approved
----------------------------------	--

