

Product data sheet

Specifications



Repacked, mounting box, Mureva Styl, 1 gang, white

MUR39911W



This repacked option saves 0.288 over the standard condition

Main

Range of product	Mureva Styl
Product or component type	Mounting box
Range compatibility	Mureva Styl enclosure
Colour tint	White (RAL 9003)

Complementary

Device mounting	Surface
cable entry	Easy valve access
Condition of use	Indoor/outdoor
Material	SEBS PP (polypropylene)
Length	76 mm
Height	54 mm
Width	76 mm
Depth	54 mm
Chemical and detergent products resistance	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Quality labels	AENOR NF
IP degree of protection	IP55
IK degree of protection	IK08
Flame retardance	Self-extinguishing 650 °C conforming to IEC 60695-2-1
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-25...55 °C

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number of Units in Package 1	1
Package 1 Height	5.400 cm
Package 1 Width	7.700 cm
Package 1 Length	7.700 cm
Package 1 Weight	76.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	45
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.896 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0.3 kg CO2 eq.

Use Better



Materials and Substances

SCIP Number

2c66ee7f-b39d-425f-a4af-fd0972454bc0

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Free of Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No