

Datasheet

RS Pro Straight 75 Ω Cable Mount BNC Connector, jack, Crimp Termination RG59 Nickel

RS Stock No: **546-3850**



Product Details

RS Pro straight cable mount BNC connector plug features a crimp ferrule, nickel plated body, gold plated centre contact and is for use with a variety of RF coaxial cable types. This female connector plug has 75 Ω impedance. It operates at a voltage rating of 335 V and temperature rating of -65 to +85°C. This connector plug is suitable for a variety of applications including video signalling and test equipment.

Features and Benefits

- Brass construction with nickel and gold plated contacts
- Crimp termination method
- Female connector
- RS BNC connectors are suitable for a variety of applications including video signalling and test equipment

**Specifications:**

Body Orientation	Straight
Body Plating	Nickel
Cable Type	RG59
Contact Material	Brass
Contact Plating	Gold
Gender	Female
Impedance	75 Ω
Mounting Type	Cable Mount
Polarity	Normal
Termination Method	Crimp
Standards Met	RoHS Compliant