

COMBINATION WRENCHES - METRIC | E110101



Description

- ISO 691 - ISO 1711-1 - ISO 3318 - ISO 7738 - DIN 3113
- 12-point OGV® ring angled at 15°.
- Open end angled at 15° from handle axis.
- OGV® profile maximizing the contact surface with the nut for a longer lifetime.
- Forged in Chrome Vanadium steel.
- High chrome finish.

Information

EAN	3258951101018
------------	---------------

A [mm]	34
---------------	----

B [mm]	68.7
---------------	------

B1 [mm]	49.3
----------------	------

C [mm]	11.5
---------------	------

C1 [mm]	17.2
----------------	------

L [mm]	380
---------------	-----

Conditioning	1
---------------------	---

[g]	639
------------	-----

