



## Datasheet

# RS PRO FULLY-COATED BALL-LOCK STAINLESS STEEL CABLE TIES, YELLOW

EN



### Technical Information:

**Material:** Stainless Steel Grade 316

316 grade stainless steel, for extra corrosive environments

**Coating:** Polyester

**Working Temp.:** -80°C to +150°C

**Description:** Entirely Yellow

**Flammability:** Fireproof

**Other Properties:** UV-resistant, Halogen free, non toxic

**Product Feature:** Fully coated version with non-toxic, halogen free polyester coating, preventing static electricity.

Provide additional edge protection.

Prevent the corrosion between dissimilar materials.

**Applications:** Ideal for petrochemical, industries, power stations, mining, ship-building, offshore, and other aggressive environments.

## Specification

RS CODE	EASE CODE	LENGTH		WIDTH		THICKNESS		MAX. BUNDLE DIAMETER		MIN. TENSILE STRENGTH	
		mm	inch	mm	inch	mm	inch	mm	inch	N	lbs
	CT-SS-BL-100/4.6FC-YL	100	3.9	4.6	0.18	0.35	0.014	25	1.00	900	200
	CT-SS-BL-125/4.6FC-YL	125	4.9					31	1.23		
	CT-SS-BL-150/4.6FC-YL	150	5.9					37	1.46		
	CT-SS-BL-200/4.6FC-YL	200	7.9					50	1.97		
	CT-SS-BL-360/4.6FC-YL	360	14.2					90	3.55		
	CT-SS-BL-200/7.9FC-YL	200	7.9	7.9	0.31	0.35	0.014	50	1.97	1200	270
	CT-SS-BL-360/7.9FC-YL	360	14.2					90	3.55		