

LMEG08

8" LED Monitor Glass Fronted Metal Case





The LMEG08 8" LED Monitor offers excellent picture quality and a sleek and pleasant design normally associated with higher end units. An impressive 500:1 contrast ratio and 800 x 600 resolution and response time of 10-15ms gives you the ultimate performance and delivers crisp clear images.

VGA & BNC input capabilities providing various connection options. The slim design maximises desktop space and makes a perfect fit for almost any office or commercial application. The desk mount can be easily removed to allow the monitor to be fitted with any 75mm VESA accessories.

Key Features

- POS / ATM Terminals
- 800 (H) x 600 (V) Resolution
- Wide Viewing Angle
- High Contrast Ratio

- Multi language OSD
- Desktop or Wall Mount
- Fast Response Rate
- Complete with Power Supply








LMEG08 8" LED Monitor


IN / OUT INTERFACE

Specifications

| Description / Model | LMEG08 |
|----------------------------------|--|
| MONITOR SPECIFICATION | |
| Panel Type | 8" (4:3) LED Monitor With Glass Front |
| Case Type | Metal |
| Maximum Resolution | 800 (H) x 600 (V) |
| Active Display Area | 162.0 x 121.5 (V) m m |
| Pixel Pitch | 0.675 (H) x 0.2025 (V) mm |
| Bezel Thickness | 22mm |
| Contrast Ratio | 500 : 1 Ratio |
| Brightness | 250 cd/ m² |
| Response time | 10ms - 15ms |
| Viewing Angle | U/D: 50° / 70°, L/R: 70° / 70° |
| Display Colours | 16.7 M |
| Video Synchronization | Yes |
| PC Compatible Frequency | 30-80KHz(H) / 50-75Hz(V) Max. 800 x 600 |
| Adjustable Colour Temperature | 9300K / 6500K / 5800K / User |
| Video Compatiblity | Multi-Standard for NTSC / PAL |
| Aspect Ratio | 4 : 3 Ratio |
| VGA Auto Frequency Correction | Yes |
| Number of Speakers | No |
| Sound Demodulation | N/A |
| Mute | N/A |
| Work Temperature / Humidity | Temperature: -10 to 50 °C Humidity: 20 % - 70 % |
| Volume +/- Power On/Off | Power ON/OFF Only |
| OSD Control | Contrast, Brightness, Language, Colour, Rotation up/down & L/R, Input Source (VGA,AV1AV2), Reset |
| OSD Language | English, French, German, Spanish, Italian, Russian, Polish and Portuguese |

| III OOT III TERI ACE | |
|----------------------|---|
| Video Interface | VGA In BNC In x 2 |
| Audio Interface | None |
| Power Interface | AC In x 1 |
| Termination | 75 Ohms (Automatic termination) |
| Safety & EMC | ROHS-2, CE, FCC, C-Tick, E13, WEEE |
| Vesa Standard Mount | 75mm x 75mm |
| Stand Type | Multi Fun ctional Desktop/Wall mount |
| Colour | Black |
| Packing Dimension | 283 (W) x 295 (H) x 105 (D) mm |
| NET Weight | 1.4 Kgs |
| GROSS Weight | 2.0 Kgs |
| POWER | |
| Power Supply | 12VDC, 1 amp |
| Voltage | AC100 - 240V 50 / 60Hz |
| Power Consumption | < 12W in "ON" |
| Accessories | Power Supply, Remote Control, Multi Functional Bracket Desktop/Wall Mount, User Manual. |
| | |
| | |





NB. Specification subject to change without notification

